



YHO100, Aluminum Overhead Tap Connector, AL, CU, ACSR, AAAC, Steel

By Burndy
Catalog # [YHO100](#)



AL Overhead Compression Tap Connector, Accommodates: AL, CU, ACSR, AAAC and Steel, Length: 1.25 IN

Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	#6-#1
Conductor - ACSR Cmpt Run	• #6 • 4 AWG • 3 AWG • #1
Conductor - AL Str Run Range	#6 - #1
Conductor - AL Str Run	#6 - #1
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-3 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 2 AWG

Conductor - ACSR Str Run Range	• 1 AWG • 3 AWG 6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	6 AWG-1 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG

- 3 AWG
- 2 AWG
- 1 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	28.4 mm
Dimension - Height inch	1.12 in
Dimension - Height fraction	1-3/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	32 mm
Dimension - Width fraction	7/10 in
Dimension - Width mm	18 mm
Dimension - Width inch	0.70 in
Dimension - Length Overall inch	1.25 in

General

Product Family	Utility Overhead & Underground
	Distribution>Compression Tap

	Connectors>H-Taps
Trade Name	HYCRIMP™
Die Index	O
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYCRIMP
Product Type	Compression
UPC	781810139004
Type	YHO
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810139004

Logistics

Minimum Pack Quantity	25
Pallet Quantity	11550
Carton Quantity	350

Product Assets

[Catalog \[English\]](#)

