



YHO100J1444, Stirrup

By Burndy
Catalog # [YHO100J1444](#)

HYCRIMP™ STIRRUP.



Features

- HYCRIMP STIRRUP

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	6 AWG 4 AWG 3 AWG 2 AWG 1 AWG
Conductor - AL Str Size Range	6 AWG-1 AWG
Conductor - ACSR Str Size	6 (6/1) Turkey AWG 5 (6/1) Thrush AWG 4 (6/1) Swan AWG 4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Dimension - Pad Width inch	5.00 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	1-1/2 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	1.50 in
Dimension - D inch	3.00 in
Dimension - Length Overall inch	12.0 in

General

Plated	Y
Trade Name	HYCRIMP™
Die Index	O
UPC	781810035078
Type	Bail
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810035078
UPC 14 Digit GTIN	00781810035078

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2688
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)