

YHO125, H-shaped Aluminum Connector

By Burndy

Catalog # [YHO125](#)

Wide range taking H-style AL connector; prefilled with PENETROX™



Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	6 AWG-1/0 AWG
Conductor - ACSR Cmpt Run	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Run Range	#6 - 1/0
Conductor - AL Str Run	#6 - 1/0
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG

Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	6 AWG-1/0
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0
Conductor - Copper Solid Run Range	6 AWG-2/0 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-1/0 AWG
Conductor - Copper Solid Tap	• 6 AWG

Conductor - Copper Str Tap Range	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
	6 AWG-1 AWG

Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
----------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	29.2 mm
Dimension - Height inch	1.15 in
Dimension - Height fraction	1-3/20 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	41 mm

Dimension - Width fraction	7/10 in
Dimension - Width mm	18 mm
Dimension - Width inch	0.70 in
Dimension - Length Overall inch	1.62 in

General

Trade Name	HYCRIMP™
Die Index	O
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYCRIMP
UPC	781810139059
Type	YHO
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810139059

Logistics

Minimum Pack Quantity	50
Pallet Quantity	1
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)

