

YHO150J1444, Stirrup

By Burndy
Catalog # [YHO150J1444](#)

HYCRIMP™ STIRRUP.



Features

- HYCRIMP STIRRUP

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	3 AWG - 2/0 AWG
Conductor - ACSR Str Size	• 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	3 (6/1) Swallow AWG-1/0 (6/1) Raven AWG

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Dimension - Pad Width inch	5.00 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	1-3/4 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	1.75 in
Dimension - D inch	3.00 in
Dimension - Length Overall inch	12.0 in

General

Plated	Y
Trade Name	HYCRIMP™
Die Index	O
UPC	781810053935
Type	Bail
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810053935
UPC 14 Digit GTIN	00781810053935

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2688
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)