



YHO2, H-shaped Aluminum Connector

By Burndy
Catalog # [YHO2](#)

Wide range taking H-style AL connector; prefilled with PENETROX™



Features

- LOKTAP™ compression connectors are high quality, range-taking devices accommodating many combinations of conductor
- LOKTAP™ connectors feature a C groove on both sides of the connector for use in street lighting applications

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	2 AWG-1/0 AWG
Conductor - ACSR Cmpt Run	• 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Run Range	3 AWG-2/0 AWG
Conductor - AL Str Run	• 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG

Conductor - ACSR Str Run Range	3 (6/1) Swallow AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	• 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	3 AWG-2/0 AWG
Conductor - Copper Str Run	• 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Solid Run Range	1 AWG-2/0 AWG
Conductor - Copper Solid Run	• 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Tap Range	#6-1/0
Conductor - Copper Solid Tap	• #6 • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1/0
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	28.4 mm
Dimension - Height inch	1.12 in

Dimension - Height fraction	1-3/25 in	Plated	No
Package Weight	0.000 lb.	Sub Brand	LOKTAP
Package Length	0.000 in	Product Type	Compression
Package Width	0.000 in	UPC	781810139035
Dimension - L Length Overall mm	38 mm	Type	YHO
Dimension - Width fraction	16/25 in	Material	Aluminum
Dimension - Width mm	16 mm	Plating Type	Unplated
Dimension - Width inch	0.64 in	UPC 14 Digit GTIN	00781810139035
Dimension - Length Overall inch	1.50 in		
General		Logistics	
Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps	Minimum Pack Quantity	25
Trade Name	LOKTAP™	Pallet Quantity	11550
Die Index	O	Carton Quantity	350
Prefilled Oxide Inhibitor	Y	Product Assets	
		Catalog [English]	



A Hubbell brand