



# YHSA10K10LF, Heat Shrink Locking Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YHSA10K10LF](#)



Heat Shrink Locking Fork Terminal For 12 - 10 AWG

## Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installation while maintaining proper spring retention of forks

## Application

For Use On Copper Conductor

## Specifications

|                               |                      |
|-------------------------------|----------------------|
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |

## Conductor

|                             |                 |
|-----------------------------|-----------------|
| Conductor Size              | 12 - 10 AWG     |
| Conductor - Copper Str Size | 12 AWG - 10 AWG |
| Range                       |                 |
| Conductor Type              | CU C Str-Size   |

## Configuration

|                |                       |
|----------------|-----------------------|
| Connector Type | Locking Fork Terminal |
|----------------|-----------------------|

## Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - Z inch             | 0.29 in  |
| Dimension - L Length Overall   | 32 mm    |
| Dimension - Pad Width inch     | 0.35 in  |
| Dimension - Bolt Size fraction | #8 - #10 |
| Dimension - Strip Length inch  | 11/32 in |
| Dimension - Stud Size fraction | #10      |
| Dimension - Stud Size inch     | #8 - #10 |
| Dimension - Length Overall     | 1.27 in  |
| inch                           |          |

## General

|                             |                  |
|-----------------------------|------------------|
| Sub Brand                   | HYDENT           |
| Insulation Type             | Heat Shrink      |
| Physical Attribute - Tongue | Snap Fork        |
| Type                        |                  |
| Trade Name                  | HYDENT™          |
| Plated                      | Y                |
| Insulation                  | Y                |
| Type                        | YHS, Heat Shrink |
| UPC 12 Digit                | 781810524640     |
| UPC 14 Digit GTIN           | 00781810524640   |
| Material                    | Copper           |
| Plating Type                | Tin              |
| UPC                         | 781810524640     |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Carton Quantity       | 100   |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)