



YHSA10K6LF, Heat Shrink Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K6LF](#)



Heat Shrink Locking Fork Terminal For 12 - 10 AWG

Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installation while maintaining proper spring retention of forks

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Dimensions

Package Length	6.250 in
Package Width	4.000 in

Package Weight	0.200 lb.
Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	32 mm
Dimension - Pad Width inch	0.30 in
Package Height	0.900 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size fraction	#6
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	1.27 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Snap Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810524695
UPC 14 Digit GTIN	00781810524695
Material	Copper
Plating Type	Tin
UPC	781810524695

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)