



YHSA10K8F, Heat Shrink Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K8F](#)

Heat Shrink Fork Terminal For 12 - 10 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.35 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#8
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.17 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810524725
UPC 14 Digit GTIN	00781810524725
Material	Copper
Plating Type	Tin
UPC	781810524725

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)