



# YHSA18K8F, Heat Shrink Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # [YHSA18K8F](#)



Heat Shrink Fork Terminal For 22 - 18 AWG

### Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

### Application

For Use On Copper Conductor

### Specifications

|                               |                      |
|-------------------------------|----------------------|
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |

### Conductor

|                |                                                                                           |
|----------------|-------------------------------------------------------------------------------------------|
| Conductor Size | 22 - 18 AWG                                                                               |
| Conductor Type | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |

### Configuration

|                |               |
|----------------|---------------|
| Connector Type | Fork Terminal |
|----------------|---------------|

### Dimensions

|                |          |
|----------------|----------|
| Package Length | 0.000 in |
| Package Width  | 0.000 in |

|                                 |           |
|---------------------------------|-----------|
| Package Weight                  | 0.000 lb. |
| Dimension - L Length Overall mm | 30 mm     |
| Dimension - Pad Width inch      | 0.31 in   |
| Package Height                  | 0.000 in  |
| Dimension - Bolt Size fraction  | #8        |
| Dimension - Strip Length inch   | 5/16      |
| Dimension - Stud Size inch      | #8        |
| Dimension - Length Overall inch | 1.17 in   |
| Dimension - N inch              | 0.17 in   |

### General

|                                  |                  |
|----------------------------------|------------------|
| Sub Brand                        | HYDENT           |
| Insulation Type                  | Heat Shrink      |
| Physical Attribute - Tongue Type | Fork             |
| Trade Name                       | HYDENT™          |
| Plated                           | Y                |
| Insulation                       | Y                |
| Type                             | YHS, Heat Shrink |
| UPC 14 Digit GTIN                | 00781810524923   |
| Material                         | Copper           |
| Plating Type                     | Tin              |
| UPC                              | 781810524923     |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
| Carton Quantity       | 100 |
| Pallet Quantity       | 1   |

### Product Assets

[Catalog \[English\]](#)