



YHSS10, Heat Shrink Splice For 12 - 10 AWG

By Burndy
Catalog # [YHSS10](#)

Heat Shrink Splice For 12 - 10 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	1/4 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.25 in
Dimension - L Length Overall mm	41 mm
Package Height	0.000 in
Dimension - Strip Length inch	5/16
Dimension - Length Overall inch	1.60 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 14 Digit GTIN	00781810476918
Material	Copper
Plating Type	Tin
UPC	781810476918

Logistics

Minimum Pack Quantity	100
Packaging Type	Bag
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)