



YHSS14BG10, Heat Shrink Splice For 16 - 14 AWG

By Burndy
Catalog # [YHSS14BG10](#)

Heat Shrink Splice For 16 - 14 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Length Overall	1.50 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Plated	Y
Insulation	Y
UPC 14 Digit GTIN	00781810486658
Material	Copper
Plating Type	Tin
UPC	781810486658

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	11440

Product Assets

[Catalog \[English\]](#)