



YHSS18BG10, Heat Shrink Splice For 22 - 18 AWG

By Burndy
Catalog # [YHSS18BG10](#)

Heat Shrink Splice For 22 - 18 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 20 • 18
Conductor - Copper Solid Size Range	20-18
Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - CopperWeld C Solid Size	• 20 • 18

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Length Overall	1.50 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Plated	Y
Insulation	Y
UPC 14 Digit GTIN	00781810486672
Material	Copper
Plating Type	Tin
UPC	781810486672

Logistics

Minimum Pack Quantity	5
Carton Quantity	1
Pallet Quantity	12000

Product Assets

[Catalog \[English\]](#)