

YJA12502N

By Burndy
Catalog # [YJA12502N](#)



Specifications

Standards - RoHS Compliance CM
Status

Conductor

Conductor - Copper Str Size 1250 kcmil
Range
Conductor - Copper Str Size 1250 kcmil

Configuration

Physical Attribute - Number of 2
Holes
Connector Type Terminal

Current

Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch 2.65 in
Package Height 0.000 in
Physical Attribute - Tongue Straight
Angle
Dimension - B Length fraction 2-3/4 in
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in
Dimension - Z inch 0.69 in
Dimension - L Length Overall 197 mm
mm
Dimension - B Length inch 2.78 in
Dimension - Outside Diameter 1.88 in
inch

Dimension - D inch 3.06 in
Dimension - N inch 0.62 in
Dimension - Inside Diameter 1.33 in
inch
Dimension - Hole Size mm 14 mm
Dimension - Hole Size inch 0.56 in
Dimension - Length Overall 7.75 in
inch

General

Feature - Barrel Type Standard
Feature - Barrel Style Chamfered
Plated Y
Physical Attribute - Tongue Standard
Type
Die Index CSA34CU
UPC 781810447840
Material Copper
Plating Type Tin - Electro Plated
UPC 12 Digit 781810447840
UPC 14 Digit GTIN 00781810447840

Logistics

Pallet Quantity 1200
Carton Quantity 5

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)