



YKA282N, Copper Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA282N](#)



HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, 4/0 Str Cu, 1/2" Stud

Features

- Tin-plated copper compression terminal with fixed hardware for making disconnectable tap or jumper connections
- Used with slotted Type YTA-2N T-Tap or YSA-R-2N terminal
- Supplied with tin-plated silicon bronze bolts and washer-face nuts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
Physical Attribute - Tongue Angle	Straight

Dimension - B Length fraction	1-31/50 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	136 mm
Dimension - B Length inch	1.62 in
Dimension - Outside Diameter inch	0.89 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.35 in
Dimension - Strip Length inch	1- 11/16 in
Dimension - Stud Size inch	1/2 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	• 168 • 208
UPC	781810014899
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810014899

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1850
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)