



YKA2R2N, Aluminum Terminal

By Burndy
Catalog # [YKA2R2N](#)

Al Compression terminal, #2 str(.316)(.325), 6-1 str 7-1 str, 5.52"L, B-G or 243 index



Features

- Aluminum compression terminal with fixed hardware and positioning pin for making disconnectable tap or jumper connections
- Used with Slotted YTA-R-2N T-Tap or YSA-R-2N Terminal (sold separately)
- Supplied with aluminum bolts and washer
- Pre-filled with PENETROX Joint Compound and Capped

Application

For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors And Making Disconnectable Tap Or Jumper Connections

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	2 AWG
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Pad Configuration	Straight
--	----------

Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.65 in
Dimension - L Length Overall mm	140 mm
Package Height	0.000 in
Dimension - B Length inch	1.68 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	5.50 in

General

Die Index	• BG • 243
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Plated	N
Type	YKA-R-2N, Disconnectable
UPC 14 Digit GTIN	00781810016985
Material	Aluminum
Plating Type	Unplated
UPC	781810016985

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	1050

Product Assets

[Catalog \[English\]](#)