

YKA321ACG1, Cast Aluminum Terminal

By Burndy
Catalog # [YKA321ACG1](#)

Cast Aluminum Compression Terminal



Features

- Cast Aluminum Compression Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Copper Str Size	350 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3-3/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in

Package Width	0.000 in
Dimension - L Length Overall mm	182 mm
Dimension - B Length inch	3.06 in
Dimension - Outside Diameter inch	1.24 in
Dimension - D inch	3 in
Dimension - N inch	0.62 in
Dimension - Inside Diameter inch	0.72 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.16 in

General

Plated	Y
Die Index	• 317 • M
Oxide Inhibitor Type	Penetrox A
UPC	781810468289
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810468289
UPC 14 Digit GTIN	00781810468289

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)