



YKA37R2N, Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA37R2N](#)



Disconnectable Terminal (With Fixed Hardware), 477 (24-7, 26-7, 30-7) ACSR 556.5 (19, 37) Al, 7-3/8 in L

Features

- Aluminum compression terminal with fixed hardware and positioning pin for making disconnectable tap or jumper connections
- Used with Slotted YTA-R-2N T-Tap or YSA-R-2N Terminal (sold separately)
- Supplied with aluminum bolts and washer
- Pre-filled with PENETROX Joint Compound and Capped

Application

For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors And Making Disconnectable Tap Or Jumper Connections

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	• 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil • 477. (30/7) Hen kcmil
Conductor - AL Str Size	556 kcmil

Configuration

Physical Attribute - Pad Configuration	Straight
--	----------

Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	187 mm
Dimension - Pad Width inch	1.90 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	7.375 in

General

Die Index	M
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Plated	N
Type	YKA-R-2N, Disconnectable
UPC 14 Digit GTIN	00781810017043
Material	Aluminum
Plating Type	Unplated
UPC	781810017043

Logistics

Minimum Pack Quantity	1
Carton Quantity	6
Pallet Quantity	630

Product Assets

[Catalog \[English\]](#)