



YKA392N, Copper Disconnectable Terminal w/ Fixed Hardware

By Burndy
Catalog # [YKA392N](#)



HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, 750 KCMIL Cu, 1/2" Stud

Features

- Tin-plated copper compression terminal with fixed hardware for making disconnectable tap or jumper connections
- Used with slotted Type YTA-2N T-Tap or YSA-R-2N terminal
- Supplied with tin-plated silicon bronze bolts and washer-face nuts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	750 kcmil
Range	
Conductor - Copper Str Size	750 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	2.31 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight

Dimension - B Length fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall	183 mm
Dimension - B Length inch	3 in
Dimension - Outside Diameter	1.7 in
inch	
Dimension - N inch	0.63 in
Dimension - Length Overall	7.22 in
inch	
Dimension - Strip Length inch	1- 3/16 in
Dimension - Stud Size inch	1/2 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	627
UPC	781810081112
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810081112

Logistics

Minimum Pack Quantity	5
Pallet Quantity	555
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)