



YKA4C2N, Copper Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA4C2N](#)



HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, #4 STR Cu, 1/2" Stud

Features

- Tin-plated copper compression terminal with fixed hardware for making disconnectable tap or jumper connections
- Used with slotted Type YTA-2N T-Tap or YSA-R-2N terminal
- Supplied with tin-plated silicon bronze bolts and washer-face nuts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4 AWG
Range	
Conductor - Copper Str Size	4 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.88 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight

Dimension - B Length fraction	1-4/57 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall	129 mm
Dimension - B Length inch	1.07 in
Dimension - Outside Diameter	0.5 in
Dimension - N inch	0.62 in
Dimension - Length Overall	5.06 in
Dimension - Strip Length inch	1- 3/16 in
Dimension - Stud Size inch	1/2 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	163
UPC	781810185988
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810185988

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)