

YNA32R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA32R](#)

Two hole compression terminal



Features

- ACSR Compression Terminal
- 2-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	395.1-395.2
Conductor - ACAR Str Size	395.1-395.2
Conductor - AL Str Size	• 336.4 • 350
Conductor - AL Str Size Range	336.4-350
Conductor - ACSR Str Size	• 300.0 (26/7) Ostrich • 336.4 (18/1) Merlin • 336.4 (26/7) Linnet • 336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich-336.4 (30/7) Oriole

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	228 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Length Overall inch	8.96 in

General

Trade Name	HYLUG™
Die Index	717
UPC	781810822104
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810822104
UPC 14 Digit GTIN	00781810822104

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)