



YNA32R4N, ACSR - Compression Terminal

By Burndy
Catalog # [YNA32R4N](#)

Two hole compression terminal



Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	• 395.1
Range	• 395.2
Conductor - ACAR Str Size	• 395.1
	• 395.2
Conductor - AL Str Size	• 356.4
	• 350
Conductor - AL Str Size Range	• 356.4
	• 350
Conductor - ACSR Str Size	• 300.0 (26/7) Ostrich
	• 336.4 (18/1) Merlin
	• 336.4 (26/7) Linnet
	• 336.4 (30/7) Oriole
Conductor - ACSR Str Size	300.0 (26/7) Ostrich-336.4
Range	(30/7) Oriole

Configuration

Physical Attribute - Pad	Straight
Orientation	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	232 mm
Dimension - B Length inch	3.9 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Length Overall inch	9.14 in

General

Trade Name	HYLUG™
Die Index	717
UPC	781810180174
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180174
UPC 14 Digit GTIN	00781810180174

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)