

# YNA32RT, 2-hole Aluminum Terminal

By Burndy  
Catalog # [YNA32RT](#)

Two hole compression terminal for extra high voltage application



**Features**

- Aluminum Compression Terminal
- 2-Hole Pad

**Specifications**

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| Certification - CSA Approved       | No |

**Conductor**

|                                 |                                                                                                                                                                  |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACAR Str Size Range | <ul style="list-style-type: none"><li>• 395.1</li><li>• 395.2</li></ul>                                                                                          |
| Conductor - ACAR Str Size       | <ul style="list-style-type: none"><li>• 395.1</li><li>• 395.2</li></ul>                                                                                          |
| Conductor - AL Str Size         | <ul style="list-style-type: none"><li>• 336.4</li><li>• 350</li></ul>                                                                                            |
| Conductor - AL Str Size Range   | 336.4-350                                                                                                                                                        |
| Conductor - ACSR Str Size       | <ul style="list-style-type: none"><li>• 300.0 (26/7) Ostrich</li><li>• 336.4 (18/1) Merlin</li><li>• 336.4 (26/7) Linnet</li><li>• 336.4 (30/7) Oriole</li></ul> |
| Conductor - ACSR Str Size Range | <ul style="list-style-type: none"><li>• 300.0 (26/7) Ostrich</li><li>• 336.4 (18/1) Merlin</li><li>• 336.4 (26/7) Linnet</li><li>• 336.4 (30/7) Oriole</li></ul> |

**Configuration**

|                                      |          |
|--------------------------------------|----------|
| Physical Attribute - Number of Holes | 2        |
| Connector Type                       | Terminal |

**Dimensions**

|                                              |          |
|----------------------------------------------|----------|
| Dimension - Pad Width inch                   | 1.68 in  |
| Dimension - Bolt Hole Size inch              | 0.56 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm              | 232 mm   |
| Dimension - Outside Diameter inch            | 1.19 in  |
| Dimension - Width fraction                   | 1.68 in  |
| Dimension - Hole Size inch                   | 0.56 in  |
| Dimension - Length Overall inch              | 9.14 in  |

**General**

|                   |                |
|-------------------|----------------|
| Trade Name        | HYLUG™         |
| Die Index         | 717            |
| UPC               | 781810514825   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810514825   |
| UPC 14 Digit GTIN | 00781810514825 |

**Logistics**

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |
| Carton Quantity       | 25   |

**Product Assets**

[Catalog \[English\]](#)