



YNA32RT15, 2-hole Aluminum Terminal 15° angle

By Burndy
Catalog # [YNA32RT15](#)

Two hole compression terminal for extra high voltage application, 15 Degree



Features

- Aluminum Compression Terminal
- 15 Degree Angle
- 2-Hole

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	• 395.1
Range	• 395.2
Conductor - ACAR Str Size	• 395.1
	• 395.2
Conductor - AL Str Size	• 336.4
	• 350
Conductor - AL Str Size Range	336.4-350
Conductor - ACSR Str Size	• 336.4 (26/7) Linnet kcmil
	• 336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-336.4 (30/7) Oriole kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
Dimension - Bolt Hole Size inch	0.56 in

Physical Attribute - Tongue Angle	15 Degree
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	230 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Length Side A inch	9.04 in
Dimension - Length Side B inch	9.14 in
Dimension - Width fraction	1.68 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	9.04 in

General

Trade Name	HYLUG™
Die Index	717
UPC	781810514832
Material	Aluminum
UPC 12 Digit	781810514832
UPC 14 Digit GTIN	00781810514832

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)