



YNA32RT15H, 2-hole Aluminum Terminal 15° angle

By Burndy
Catalog # [YNA32RT15H](#)



Two hole compression terminal for extra high voltage application,
15 Degree

Features

- Aluminum Compression Terminal
- 15 Degree Angle
- 2-Hole

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	• 395.1 • 395.2
Conductor - ACAR Str Size	• 395.1 • 395.2
Conductor - AL Str Size	• 336.4 • 350
Conductor - AL Str Size Range	• 336.4 • 350
Conductor - ACSR Str Size	• 300.0 (26/7) Ostrich • 336.4 (18/1) Merlin • 336.4 (26/7) Linnet • 336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	• 300.0 (26/7) Ostrich • 336.4 (18/1) Merlin • 336.4 (26/7) Linnet • 336.4 (30/7) Oriole

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
Dimension - Bolt Hole Size inch	0.56 in
Physical Attribute - Tongue Angle	15 Degree
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	230 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Width fraction	1.68 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	9.04 in

General

Trade Name	HYLUG™
Die Index	717
UPC	781810514849
Material	Aluminum
UPC 12 Digit	781810514849
UPC 14 Digit GTIN	00781810514849

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)