



YNA34R, 2-hole Aluminum Terminal

By Burndy
Catalog # [YNA34R](#)

Two hole compression terminal



Features

- Aluminum Compression Terminal
- 2-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397.5 400 450 477
Conductor - AL Str Size Range	397.5-477
Conductor - ACSR Str Size	397.5 (18/1) Chickadee 397.5 (24/7) Brant 397.5 (26/7) Ibis 397.5 (30/7) Larkspur
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee-397.5 (30/7) Larkspur

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.78 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	231 mm
Dimension - Outside Diameter inch	1.3 in
Dimension - Width fraction	1.78 in
Dimension - Length Overall inch	9.08 in

General

Trade Name	HYLUG™
Die Index	719
UPC	781810016183
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016183
UPC 14 Digit GTIN	00781810016183

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)