



YNA36R15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA36R15](#)



Two hole compression terminal, 15 Degree

Features

- Aluminum Compression Terminal
- 15 Degree Angle
- 2-Hole

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 500 • 550 • 556.5
Conductor - AL Str Size Range	500-556.5
Conductor - ACSR Str Size	• 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477.0 (26/7) Hawk kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.96 in
----------------------------	---------

Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	244 mm
Dimension - Outside Diameter inch	1.41 in
Dimension - Length Side A inch	9.62 in
Dimension - Length Side B inch	9.47 in
Dimension - Width fraction	1.96 in
Dimension - Length Overall inch	9.62 in

General

Trade Name	HYLUG™
Die Index	720
UPC	781810180211
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180211
UPC 14 Digit GTIN	00781810180211

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)