



# YNA36R90, 4-hole Aluminum Terminal 90° Angle

By Burndy  
Catalog # [YNA36R90](#)

Four hole compression terminal, 90 Degree



## Features

- Aluminum Compression Terminal
- 90 Degree Angle
- 4-Hole

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                                 |                                                                                                                                                              |
|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size         | <ul style="list-style-type: none"><li>• 500</li><li>• 550</li><li>• 556.5</li></ul>                                                                          |
| Conductor - AL Str Size Range   | 500-556.5                                                                                                                                                    |
| Conductor - ACSR Str Size       | <ul style="list-style-type: none"><li>• 477.0 (18/1) Pelican</li><li>• 477.0 (24/7) Flicker</li><li>• 477.0 (26/7) Hawk</li><li>• 477.0 (30/7) Hen</li></ul> |
| Conductor - ACSR Str Size Range | 477.0 (18/1) Pelican-477.0 (30/7) Hen                                                                                                                        |

## Configuration

|                                      |           |
|--------------------------------------|-----------|
| Physical Attribute - Pad Orientation | 90 Degree |
| Connector Type                       | Terminal  |

## Dimensions

|                                              |          |
|----------------------------------------------|----------|
| Dimension - Bolt Hole Size inch              | 0.56 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm              | 145 mm   |
| Dimension - Length Overall inch              | 5.7 in   |

## General

|                           |                |
|---------------------------|----------------|
| Trade Name                | HYLUG™         |
| UPC                       | 781810157794   |
| Prefilled Oxide Inhibitor | Y              |
| Material                  | Aluminum       |
| UPC 12 Digit              | 781810157794   |
| UPC 14 Digit GTIN         | 00781810157794 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 450 |
| Carton Quantity       | 5   |

## Product Assets

[Catalog \[English\]](#)