



YNA39R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA39R](#)

Two hole compression terminal



Features

- Compression Terminal with 2-hole pad

Application

For use on: ACSR, ACAR and SAC Transmission Lines

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - AL Str Size	• 600 kcmil • 636 kcmil • 650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	2

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	2.08 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	250 mm
Dimension - Outside Diameter inch	1.5 in
Dimension - Width fraction	2.08 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	9.84 in

General

Trade Name	HYLUG™
Die Index	722
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016343
Type	YNS-R
Material	Aluminum
UPC 12 Digit	781810016343
UPC 14 Digit GTIN	00781810016343

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)