



YNA43R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA43R](#)

Four hole compression terminal

Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil
Conductor - ACSR Str Size	• 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	4

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.07 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	256 mm
Dimension - Outside Diameter inch	1.61 in
Dimension - Width fraction	3.07 in
Dimension - Length Overall inch	10.07 in

General

Trade Name	HYLUG™
Die Index	724
UPC	781810016350
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016350
UPC 14 Digit GTIN	00781810016350

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)