



YNA43R45, ACSR - Compression Terminal

By Burndy
Catalog # [YNA43R45](#)

Aluminum Compression Terminal 230 kV, 605-666.6 kcmil ACSR,
700-800 kcmil Alum., 45 Deg



Features

- ACSR Compression Terminal
- 45 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil
Conductor - ACSR Str Size	• 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Physical Attribute - Pad Orientation	45 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.07 in
Dimension - Height inch	6.26 in
Dimension - Height fraction	6-13/50 in
Dimension - L Length Overall mm	216 mm
Dimension - B Length inch	4.53 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Length Overall inch	8.51 in

General

Trade Name	HYLUG™
Die Index	724
UPC	781810283929
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810283929
UPC 14 Digit GTIN	00781810283929

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)