

YNA43R90, ACSR - Compression Terminal

By Burndy
Catalog # [YNA43R90](#)

Four hole compression terminal, 90 Degree



Features

- ACSR Compression Terminal
- 90 Degree Angle
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil
Conductor - ACSR Str Size	• 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Physical Attribute - Pad Orientation	90 Degree
--------------------------------------	-----------

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Height inch	6.25 in
Dimension - Height fraction	6-1/4 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	155 mm
Dimension - B Length inch	4.88 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Width fraction	3.00 in
Dimension - Length Overall inch	6.09 in

General

Trade Name	HYLUG™
Die Index	724
UPC	781810221945
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810221945
UPC 14 Digit GTIN	00781810221945

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)