



YNA43RH, Aluminum Terminal with Hardware Kit

By Burndy
Catalog # [YNA43RH](#)

Al Compression Terminal, 605-666.6 kcmil ACSR, 700-800 kcmil Aluminum, 230 kV, 724 Index, Supplied with hardware



Features

- Aluminum Compression Terminal
- Supplied with Hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	700 kcmil 715 kcmil 750 kcmil 795 kcmil 800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil
Conductor - ACSR Str Size	605 (24/7) Peacock kcmil 605 (26/7) Squab kcmil 605 (30/19) Teal kcmil 636 (24/7) Rook kcmil 636 (26/7) Grosbeak kcmil 636 (30/19) Egret kcmil 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	256 mm
Dimension - Outside Diameter inch	1.61 in
Dimension - Length Overall inch	10.07 in

General

Trade Name	HYLUG™
Die Index	724
UPC	781810081570
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810081570
UPC 14 Digit GTIN	00781810081570

Logistics

Minimum Pack Quantity	10
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)