



YNA451R15H, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA451R15H](#)



HYLUG™ Aluminum Compression Terminal; 15 Degree Pad; 4-Hole

Features

- ACSR Compression Terminal
- 15 Degree Angle
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	800 (37)-900 (37)
Conductor - ACAR Str Size	• 800 (37) • 850 (37) • 900 (37)
Conductor - AL Str Size	• 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Size Range	795.5-1000
Conductor - ACSR Str Size	• 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	15 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	259 mm
Dimension - Outside Diameter inch	1.8 in
Dimension - Length Overall inch	10.21 in

General

Trade Name	HYLUG™
Die Index	725
UPC	781810180280
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180280
UPC 14 Digit GTIN	00781810180280

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)