



YNA451R45, ACSR - Compression Terminal

By Burndy
Catalog # [YNA451R45](#)



Aluminum compression terminal, 715.5-874.5 Kcmil ACSR, 874.5-1000 Kcmil Aluminum cable, 45 Deg

Features

- ACSR Compression Terminal
- 45 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	850 (37)-900 (37)
Conductor - ACAR Str Size	• 850 (37) • 900 (37)
Conductor - AL Str Size	• 874.5 • 900 • 954 • 1000
Conductor - AL Str Size Range	874.5-1000
Conductor - ACSR Str Size	• 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	45 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	220 mm
Dimension - B Length inch	4.9 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Length Overall inch	8.67 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810283950
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810283950
UPC 14 Digit GTIN	00781810283950

Logistics

Minimum Pack Quantity	20
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)