

YNA451R90, ACSR - Compression Terminal

By Burndy
Catalog # [YNA451R90](#)



HYLUG™, Aluminum Compression terminal for ACSR and Stranded aluminum cable, 715.5-874.5 Kcmil ACSR, 874.5-1000 Kcmil Aluminum cable, 90 Deg

Features

- ACSR Compression Terminal
- 90 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 874.5 • 900 • 954 • 1000
Conductor - AL Str Size Range	874.5-1000
Conductor - ACSR Str Size	• 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	90 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Dimension - Height inch	6.25 in
Dimension - Height fraction	6-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	159 mm
Dimension - B Length inch	4.82 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Width fraction	3.00 in
Dimension - Length Overall inch	6.25 in

General

Trade Name	HYLUG™
Die Index	725
UPC	781810283967
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810283967
UPC 14 Digit GTIN	00781810283967

Logistics

Minimum Pack Quantity	18
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)