

YNA451RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA451RT](#)

HYLUG™, Compression Terminal , 715.5-874.5 kcmil ACSR 795-1000 kcmil ALUM.840.2-927.2 kcmil ACAR, 4 Pad holes, 10.57 in Length.



Features

- Compression Terminal with 4-hole pad

Application

For use on: ACSR, ACAR and SAC Transmission Lines

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	840.2 KCMIL - 927.2 KCMIL
Conductor - ACAR Str Size	840.2 KCMIL - 927.2 KCMIL
Conductor - AL Str Size	• 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Size Range	795.5-1000
Conductor - ACSR Str Size	• 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	268 mm
Dimension - Outside Diameter inch	1.8 in
Dimension - Width fraction	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.57 in

General

Trade Name	HYLUG™
Die Index	725
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016442
Type	YNA-RT EHV
Material	Aluminum
UPC 12 Digit	781810016442
UPC 14 Digit GTIN	00781810016442

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1008
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)