

YNA49R15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA49R15](#)

HYLUG™, Aluminum Compression Terminal for ACSR, ACAR & SAC Cables, 900-1113 Kcmil ACSR, 1033.5-1272 Kcmil SAC, 983.1-1198 Kcmil ACAR, 250 Kv Max., 10.35 IN L, 4 hole, 15 Deg



Features

- ACSR Compression Terminal
- 15 Degree Angle
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - AL Str Size	• 1033.5 • 1100 • 1192.5 • 1200 • 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	• 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	15 Degree
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	263 mm
Dimension - Outside Diameter inch	1.97 in
Dimension - Length Side A inch	10.35 in
Dimension - Length Side B inch	10.46 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	10.35 in

General

Trade Name	HYLUG™
Die Index	727
UPC	781810367766
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810367766
UPC 14 Digit GTIN	00781810367766

Logistics

Minimum Pack Quantity	1
Pallet Quantity	500
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)