



YNA49R15H, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA49R15H](#)

Comprsn Terminal For ACSR,ACAR and std Al Cable with
Hardware Kit, 727 Index



Features

- Aluminum Terminal
- 15 Degree Angle
- Supplied with Hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	950 (37)-1200 (61)
Conductor - ACAR Str Size	• 950 (37) • 1000 (61) • 1100 (61) • 1200 (61)
Conductor - AL Str Size	• 1033.5 • 1100 • 1192.5 • 1200 • 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	• 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	15 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	263 mm
Dimension - Outside Diameter inch	1.97 in
Dimension - Length Overall inch	10.35 in

General

Trade Name	HYLUG™
Die Index	727
UPC	781810055243
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810055243
UPC 14 Digit GTIN	00781810055243

Logistics

Minimum Pack Quantity	1
Pallet Quantity	500
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)