



YNA49R90, ACSR - Compression Terminal

By Burndy
Catalog # [YNA49R90](#)

HYLUG™, Aluminum Compression Terminal , 900-1113 kcmil ACSR
45-7STR 1033.5-1272 kcmil ALUM., 90 Degree



Features

- ACSR Compression Terminal
- 90 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1033.5 • 1100 • 1192.5 • 1200 • 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	• 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	90 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Height inch	6.25 in
Dimension - Height fraction	6-1/4 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	157 mm
Dimension - B Length inch	4.88 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Width fraction	3.00 in
Dimension - Length Overall inch	6.19 in

General

Trade Name	HYLUG™
Die Index	727
UPC	781810283974
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810283974
UPC 14 Digit GTIN	00781810283974

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)