

YNA49RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA49RT](#)

HYLUG™, Aluminum Compression Terminal , 900-1113 kcmil ACSR
45-7STR 1033.5-1272 kcmil ALUM.983.1-1198 kcmil ACAR ., 4 Pad
holes, 10.77 in Length.

Features

- Compression Terminal with 4-hole pad

Application

For use on: ACSR, ACAR and SAC Transmission Lines

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - AL Str Size	• 1033.5 • 1100 • 1192.5 • 1200 • 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	• 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	Straight
--------------------------------------	----------



Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	274 mm
Dimension - Outside Diameter inch	1.97 in
Dimension - Width fraction	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	10.77 in

General

Trade Name	HYLUG™
Die Index	727
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016367
Type	YNA-RT EHV
Material	Aluminum
UPC 12 Digit	781810016367
UPC 14 Digit GTIN	00781810016367

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)