



YNA49RT90, ACSR - Compression Terminal

By Burndy
Catalog # [YNA49RT90](#)

Aluminum Compression terminal, 900-954 kcmil, 90 Deg, 345 kV



Features

- ACSR Compression Terminal
- 90 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1000 (61)-1200 (61)
Conductor - ACAR Str Size	• 1000 (61) • 1100 (61) • 1200 (61)
Conductor - AL Str Size	• 1033.5 • 1100 • 1192.5 • 1200 • 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	• 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	90 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	167 mm
Dimension - B Length inch	5.18 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Length Overall inch	6.56 in

General

Trade Name	HYLUG™
Die Index	727
UPC	781810100059
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810100059
UPC 14 Digit GTIN	00781810100059

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)