



YNA52R15H, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA52R15H](#)

Comprsn Terminal For ACSR,ACAR and std Al Cable with Hardware Kit, 728 Index



Features

- ACSR Compression Terminal
- 15 Degree Angle
- Supplied with Hardware Kit

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	• 1250 (61) • 1300 (61)
Conductor - AL Str Size	• 1351.5 • 1400 • 1431.0 • 1500
Conductor - ACSR Str Size	• 1113 (54/19) Finch • 1272 (54/19) Pheasant

Configuration

Physical Attribute - Pad Orientation	15 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - L Length Overall mm	307 mm
Dimension - Outside Diameter inch	2.26 in
Dimension - Length Overall inch	12.09 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810490037
Material	Aluminum
UPC 12 Digit	781810490037
UPC 14 Digit GTIN	00781810490037

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)