



YNA52RT15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA52RT15](#)

HYLUG™, Aluminum Compression Terminal, 345 Kv, 1113.54-1351.5 Kcmil ACSR, 1351.5-1510 Kcmil Aluminum, 1277-1280 Kcmil ACAR, Cable to Flat, 15 Deg

Features

- ACSR Compression Terminal
- 15 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1277 KCMIL- 1280 KCMIL
Conductor - ACAR Str Size	1277 KCMIL- 1280 KCMIL
Conductor - AL Str Size	• 1351.5 • 1400 • 1431.0 • 1500
Conductor - AL Str Size Range	1351.5-1500
Conductor - ACSR Str Size	• 1113 (54/19) Finch kcmil • 1192.5 (45/7) Bunting kcmil • 1192.5 (54/19) Grackle kcmil • 1272 (54/19) Pheasant kcmil • 1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree
--------------------------------------	-----------



Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	321 mm
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Side A inch	12.62 in
Dimension - Length Side B inch	13.82 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	12.62 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810016404
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016404
UPC 14 Digit GTIN	00781810016404

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)