



YNA52RT30, Aluminum Terminal, 30° Angle

By Burndy
Catalog # [YNA52RT30](#)



Aluminum Compression terminal, 1113-1351.5 kcmil, 345 kV

Features

- Aluminum Compression Terminal
- 30 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1351.5 1400 1431.0 1500
Conductor - AL Str Size Range	1351.5-1500
Conductor - ACSR Str Size	1113 (54/19) Finch 1272 (54/19) Pheasant
Conductor - ACSR Str Size Range	1113 (54/19) Finch-1272 (54/19) Pheasant

Configuration

Physical Attribute - Pad Orientation	30 Degree
--------------------------------------	-----------

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - L Length Overall mm	308 mm
Dimension - B Length inch	6.36 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Overall inch	12.11 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810046272
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810046272
UPC 14 Digit GTIN	00781810046272

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)