



YNA52RT45, Aluminum Terminal, 45° Angle

By Burndy
Catalog # [YNA52RT45](#)

Aluminum Compression terminal, 1113-1351.5 kcmil, 45 Deg, 345 kV



Features

- Aluminum Compression Terminal
- 45 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1300 (61)
Conductor - ACAR Str Size	1300 (61)
Conductor - AL Str Size	1351.5 1400 1431.0 1500
Conductor - AL Str Size Range	1351.5-1500
Conductor - ACSR Str Size	1113 (54/19) Finch 1272 (54/19) Pheasant
Conductor - ACSR Str Size Range	1113 (54/19) Finch-1272 (54/19) Pheasant

Configuration

Physical Attribute - Pad Orientation	45 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - L Length Overall mm	251 mm
Dimension - B Length inch	6.36 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Overall inch	9.9 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810057759
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810057759
UPC 14 Digit GTIN	00781810057759

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)