



YNA54R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA54R](#)

HYLUG™, Aluminum Compression Terminal for ACSR,ACAR & SAC Cables, 1431 Kcmil ACSR, 1590-1600 Kcmil SAC, 1534 Kcmil ACAR , 250 Kv Max., 13.30 IN L, 4 hole

Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACAR Str Size	1534 KCMIL
Conductor - AL Str Size	1590 kcmil - 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil-1600 kcmil
Conductor - ACSR Str Size	1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1431 (54/19) Plover kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.11 in
----------------------------	---------

Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	342 mm
Dimension - Outside Diameter inch	2.25 in
Dimension - Width fraction	3.11 in
Dimension - Length Overall inch	13.46 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810128084
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810128084
UPC 14 Digit GTIN	00781810128084

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)