



# YNA54RT, ACSR - Compression Terminal

By Burndy  
Catalog # [YNA54RT](#)

HYLUG™, Al Tube Compression Terminal, 4 Holes, 1431 Kcmil  
ACSR, 1590 - 1600 Kcmil Al, 1534 Kcmil ACAR, greater than 230  
kV, 1.75" Spacing

## Features

- ACSR Compression Terminal
- 4-Hole Pad

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                                 |                         |
|---------------------------------|-------------------------|
| Conductor - ACAR Str Size Range | 1534 KCMIL              |
| Conductor - ACAR Str Size       | 1534 KCMIL              |
| Conductor - AL Str Size         | 1590 kcmil - 1600 kcmil |
| Conductor - AL Str Size Range   | 1590 kcmil - 1600 kcmil |
| Conductor - ACSR Str Size       | 1431 (54/19) Plover     |
| Conductor - ACSR Str Size Range | 1431 (54/19) Plover     |

## Configuration

|                                      |          |
|--------------------------------------|----------|
| Physical Attribute - Pad Orientation | Straight |
| Physical Attribute - Number of Holes | 4        |
| Connector Type                       | Terminal |

## Dimensions

|                                              |           |
|----------------------------------------------|-----------|
| Dimension - Pad Width inch                   | 3.22 in   |
| Dimension - Bolt Hole Size inch              | 0.56 in   |
| Package Height                               | 0.000 in  |
| Package Weight                               | 0.000 lb. |
| Package Length                               | 0.000 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in  |
| Package Width                                | 0.000 in  |
| Dimension - L Length Overall mm              | 350 mm    |
| Dimension - Outside Diameter inch            | 2.25 in   |
| Dimension - Width fraction                   | 3.22 in   |
| Dimension - Length Overall inch              | 13.79 in  |

## General

|                           |                |
|---------------------------|----------------|
| Trade Name                | HYLUG™         |
| Die Index                 | 728            |
| UPC                       | 781810016398   |
| Prefilled Oxide Inhibitor | Y              |
| Material                  | Aluminum       |
| UPC 12 Digit              | 781810016398   |
| UPC 14 Digit GTIN         | 00781810016398 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 450 |
| Carton Quantity       | 5   |

## Product Assets

[Catalog \[English\]](#)