



YNA54RT15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA54RT15](#)



HYLUG™, Aluminum Compression terminal, 1431 Kcmil
ACSR,1590-1600 Kcmil Aluminum,1534 Kcmil ACAR, Cable to
Flat, 15 Deg, Terminal available with H/W

Features

- ACSR Compression Terminal
- 15 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	1534 KCMIL
Range	
Conductor - ACAR Str Size	1534 KCMIL
Conductor - AL Str Size	1590 kcmil - 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil - 1600 kcmil
Conductor - ACSR Str Size	1431 (54/19) Plover
Conductor - ACSR Str Size	1431 (54/19) Plover
Range	

Configuration

Physical Attribute - Pad	15 Degree
Orientation	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
----------------------------	---------

Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	356 mm
Dimension - Outside Diameter inch	2.25 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	14.02 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810096192
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810096192
UPC 14 Digit GTIN	00781810096192

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)