

YNA56R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA56R](#)

HYLUG™, Al Compression Terminal for ACSR,ACAR & SAC Cables, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil SAC, 1650 Kcmil ACAR , 250 Kv Max., 12.50 IN L, 4 hole



Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1650 KCMIL
Conductor - ACAR Str Size	1650 KCMIL
Conductor - AL Str Size	• 1700 • 1750 • 1800
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL
Conductor - ACSR Str Size	1590 (54/19) Falcon
Conductor - ACSR Str Size Range	1590 (54/19) Falcon

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.44 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	324 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.44 in
Dimension - Length Overall inch	12.74 in

General

Trade Name	HYLUG™
Die Index	729
UPC	781810491300
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810491300
UPC 14 Digit GTIN	00781810491300

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)