



YNA56R15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA56R15](#)

HYLUG™, Al Compression Terminal for ACSR,ACAR & SAC
Cables, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil SAC, 1650
Kcmil ACAR , 250 Kv Max., 12.50 IN L, 4 hole, 15 Deg

Features

- ACSR Compression Terminal
- 15 Degree Angle
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1650 KCMIL (42/19 STR)
Conductor - ACAR Str Size	1650 KCMIL (42/19 STR)
Conductor - AL Str Size	• 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL
Conductor - ACSR Str Size	• 1510.5 (45/7) Nuthatch kcmil • 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil-1590 (54/19) Falcon kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree
Physical Attribute - Number of Holes	4



Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.44 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	318 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Length Side A inch	12.50 in
Dimension - Length Side B inch	12.74 in
Dimension - Width fraction	3.44 in
Dimension - Length Overall inch	12.5 in

General

Trade Name	HYLUG™
Die Index	729
UPC	781810367780
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810367780
UPC 14 Digit GTIN	00781810367780

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)